



### SPECIFICATION

Clean seal fully welded construction is finished in satin stainless steel tubing with double chrome plated innovative flange and cover system. Simple fixing method with a hygienically sealed installation with silicone 'o' ring seals. Designed for the safety, security and convenience of the physically disabled. Easy to install on most building surfaces. Tubing diameter is 32mm.

Includes premium designed durable cast alloy cradle with fully adjustable sliding tension for rail and the handset pivot incorporating a self cleaning slide with anti-rotate feature.

### OPTIONS

ASI JD MacDonald can also supply the tubing in a high polish stainless steel.


### RECOMMENDED INSTALLATION HEIGHT


To comply with Australian Standards AS 1428.1, grab rails must be fastened a minimum distance of 800mm from the floor, with 600mm of clear space above the rail and to withstand a force of 1100N at any point from any direction.

### WARRANTY

One year.

**Grab Rail GCS34** (right hand model shown) shall be Model No. GCS34 and shall be a length of 300mm or 600mm as supplied by ASI JD MacDonald. (1000mm x 760mm horizontal x 1100mm vertical).

 All ASI JD MacDonald disabled compliant products when installed must be in accordance with AS1428 to ensure the specified product is complying with all washroom specification requirements.



- Effectively sealed to inhibit bacteria
- Easy ¼ turn flange cover installation
- Silicone 'o-ring' seals